

RM129

CODE	DIAMÈTRE	MACHOIRES
RM129Y033	1/2"X(16X2)	TH-H-U
RM129Y037	1/2"X(20X2)	TH-H-U
RM129Y043	3/4"X(16X2)	TH-H-U
RM129Y047	3/4"X(20X2)	TH-H-U
RM129Y049	3/4"X(26X3)	TH-H
RM129Y059	1"X(32X3)	TH-H-U
RM129Y066	1"1/4X(40X3,5)	TH-U
RM129Y076	1"1/2X(40X3,5)	TH-U
RM129Y077	1"1/2X(50X4)	TH-U
RM129Y087	2"X(50X4)	TH-U
RM129Y088	2"X(63X4,5)	TH
RM129Y098	2"1/2X(63X4,5)	TH

□	■
10	200
10	200
10	200
10	200
5	100
5	50
1	25
1	20
1	20
1	10
1	10
1	10



Coude femelle à sertir

- Repérage du diamètre par marquage au laser
- Contrôle visuel de l'introduction du tube
- QB : N°4662-52-2010
- ACS : N° 16 ACCNY193



RM130SP

CODE	DIAMÈTRE	MACHOIRES
RM130PY023	3/8"X(16X2)	TH-H-U
RM130PY033	1/2"X(16X2)	TH-H-U
RM130PY037	1/2"X(20X2)	TH-H-U
RM130PY043	3/4"X(16X2)	TH-H-U
RM130PY047	3/4"X(20X2)	TH-H-U
RM130PY049	3/4"X(26X3)	TH-H
RM130PY058	1"X(26X3)	TH-H

□	■
10	100
10	100
10	100
10	100
10	100
5	50
5	50



Coude femelle à sertir avec écrou prisonnier

- Repérage du diamètre par marquage au laser
- Contrôle visuel de l'introduction du tube
- QB : N°4662-52-2010
- ACS : N° 16 ACCNY193



RM139

CODE	DIAMÈTRE	MACHOIRES
RM139Y033	1/2"X(16X2)	TH-H-U
RM139Y037	1/2"X(20X2)	TH-H-U
RM139Y049	3/4"X(26X3)	TH-H

□	■
10	100
5	100
5	50



Patère à sertir

- Pour connecter vos éléments sanitaires
- QB : N°4662-52-2010
- ACS : N° 16 ACCNY193



RM578G

CODE	RACC. MULTICOUCHE	ENTRAXE
RM578GY301	16 x 2	150 mm
RM578GY011	20 x 2	150 mm
RM578GY302	16 x 2	50 mm
RM578GY303	16 x 2	Mono

□	■
1	-
1	-
1	-
1	-



Patère multicouche sanitaire

- Raccordement robinetterie 1/2"

RM144

CODE	DIAMÈTRE	MACHOIRES
RM144Y009	26X3	TH-H
RM144Y011	32X3	TH-H-U
RM144Y012	40X3,5	TH-U
RM144Y013	50X4	TH-U
RM144Y014	63X4,5	TH

□	■
5	100
5	50
1	25
1	25
1	25



Coude 45° à sertir

- Repérage du diamètre par marquage au laser
- Contrôle visuel de l'introduction du tube
- QB : N°4662-52-2010
- ACS : N° 16 ACCNY193



RM150

CODE	DIAMÈTRE	MACHOIRES
RM150Y003	16X2	TH-H-U
RM150Y007	20X2	TH-H-U
RM150Y009	26X3	TH-H
RM150Y011	32X3	TH-H-U
RM150Y012	40X3,5	TH-U
RM150Y013	50X4	TH-U
RM150Y014	63X4,5	TH
RM150Y015	75X5	U
RM150Y016	90X7	U

□	■
10	100
10	100
5	50
5	40
1	10
1	10
1	5
1	4
1	-



Té égal à sertir

- Repérage du diamètre par marquage au laser
- Contrôle visuel de l'introduction du tube
- QB : N°4662-52-2010
- ACS : N° 16 ACCNY193

